DEUTERIUM ARC LAMP - P716

UV Light Source for Spectroscopy - 3 volt

Instrument

Waters 484

Electrical

Filament/Heater Voltage Start 3.0 VDC
Operating 1.5~2.0 VDC
Filament/Heater Current Warm-up 4.5A Max
Operating 3.5A Max

Discharge/Arc Voltage Strike @25° > 250VDC

Operating 60 - 90 VDC

Discharge/Arc Current 10 - 300mA

Leads Black Filament & Cathode

Red Anode


Terminals 3-Pin Housing

Optical

Window UV Transmitting Borosilicate

Aperture type 1mm Circular Wavelength range 185nm - 400nm

Noise $< 1 \times 10^{-4}$ Absorption units Drift $< 3 \times 10^{-3}$ Absorption units



Dimensions in millimetres

When radiant energy reaches 50% of the initial energy. Typical life 1500 hours

This Deuterium lamps is guaranteed for a period of one year from date of delivery or 1000 hours usage, which ever comes first.


Warranty

Operational life

Free of charge replacement lamp will be provided where Photron is satisfied the following conditions have been adhered to.

- · Lamp is returned to supplier freight paid.
- Lamp has been operated within our recommended specifications.
- Lamp has not failed due to accidental, misuse or transit damage.
- If a replacement lamp is supplied the validity of guarantee shall commence from delivery date of original lamp.

Spectrum of Deuterium Emissions



Precautions for use

- Do not subject the lamp to mechanical shock.
- Ensure glass envelope is free from foreign material. Lamp may be wiped using alcohol liquid.
- · Caution! UV transmitting window is very thin. Handle with care.
- Care must be taken not to contact lamp with bare hand, temperature can reach over 200°C during operation.
- UV Radiation is harmful to the eyes. Do not observe light output directly.
- Deuterium lamps operate at high voltages. Extreme caution is required to prevent electrical shock.



Unit 5 - 3 Vesper Drive, Narre Warren, Victoria, Australia 3805

Tel: 6-13-9704-9933 • Fax: 6-13-9704-6289

sales@photron.com.au • service@photron.com.au www.photronlamp.com

Quality Certified for ISO9001:2000